

Product data sheet

Characteristics

LZ8H6X5FU

TeSys, Reversing ultra compact starter, TeSys Hybrid, Safe Torque Off, 3P, 500VAC, 3kW at 400V, 110 to 230VAC



Main

Range	TeSys
Product name	TeSys Hybrid
Device short name	LZ8H
Product or component type	Reversing ultra-compact starter
Motor starter type	Direct on line
Poles description	3P
[Ue] rated operational voltage	500 V AC
[Ie] rated operational current	6.5 A at 500 V AC-53A 9 A at 500 V AC-51 4.5 A at 500 V AC-53A mounting side by side 6 A at 500 V AC-51 mounting side by side
Thermal protection adjustment range	1.5...9 A
Motor power kW	1.5 kW at 220 V AC 0.65 1.5 kW at 230 V AC 0.65 2.2 kW at 380 V AC 0.65 3 kW at 400 V AC 0.65 3 kW at 415 V AC 0.65 3 kW at 440 V AC 0.65 3 kW at 500 V AC 0.65
Motor power hp	1 Hp at 200 V AC 1.5 Hp at 230 V AC 3 hp at 460 V AC
[Uc] control circuit voltage	110...230 V AC 50/60 Hz
Safety level	SIL 3 conforming to IEC 61508-1 stop function PL = e conforming to ISO 13849-1 stop function SIL 2 conforming to IEC 61508-1 motor protection
Safety reliability data	SFF = 99 % stop function SFF = 99 % motor protection MTTFd = 289 years stop function MTTFd = 273 years motor protection PFHd = 6.82E-9 1/h stop function
Thermal overload class	Class 10A conforming to IEC 60947-4-2

Complementary

Auxiliary contact composition	1 C/O fault signalling
Control circuit voltage limits	85...253 V AC
Current consumption	<= 4 mA at 110...230 V AC
Reset	Manual Electrical reset
Electrical durability	30 Mcycles
Maximum operating rate	120 Cyc/Mn AC-51 50 % ON 6 cyc/mn AC-53A 50 % ON
Mounting mode	By clips
Mounting support	DIN rail
Connections - terminals	Screw clamp terminals 1 cable(s) 0.2...2.5 mm ² - rigid Screw clamp terminals 1 cable(s) 0.25...2.5 mm ² - flexible - with cable end Screw clamp terminals 1 cable(s) 0.2...2.5 mm ² - flexible - without cable end

Tightening torque	0.5...0.6 N.m flat Ø 2.5 mm screwdriver 3 mm
Certifications	CULus CE ATEX as associated device for motor protection in zones 1 and 21
Standards	UL 60947-4-1 IEC 60947-4-2
[Ui] rated insulation voltage	500 V AC 50/60 Hz
[Uimp] rated impulse withstand voltage	4 kV
Pollution degree	2
Width	22.5 mm
Height	99 mm
Depth	114.5 mm
Net weight	212 g





Environment

IP degree of protection	IP20
Protective treatment	TC
Ambient air temperature for operation	-25...30 °C without derating 30...70 °C with derating
Ambient air temperature for storage	-40...80 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.6 cm
Package 1 Width	11.7 cm
Package 1 Length	11.9 cm
Package 1 Weight	272 g
Unit Type of Package 2	S01
Number of Units in Package 2	10
Package 2 Height	15 cm
Package 2 Width	15 cm
Package 2 Length	40 cm
Package 2 Weight	2.89 kg

Offer Sustainability

REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins