

Product data sheet

Characteristics

MCB4-163

Miniature circuit breaker, Clipsal Resi MAX, 1P
63 A C curve 4500 A 240 V

Main

Product brand	Clipsal
Range	Resi MAX

Complementary

Curve code	C
Number of poles	1
[In] rated current	63 A
Number of modules	1
[Ue] rated operational voltage	240 V
Breaking capacity	Icn 4500 A at 240 V conforming to AS/NZS 60898-1
Network type	AC
Network frequency	50/60 Hz
[Uimp] rated impulse withstand voltage	4 kV
[Ui] rated insulation voltage	440 V
Mechanical durability	20000 cycles
Electrical durability	10000 cycles
Connections - terminals	Screw terminal for 1 cable(s) 0.5...35 mm ² rigid Screw terminal for 1 cable(s) 0.5...25 mm ² flexible Screw terminal for 1 cable(s) 0.5...25 mm ² flexible with ferrule
Wire stripping length	13 mm
Tightening torque	3.5 N.m

Environment

IP degree of protection	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...70 °C
Standards	AS/NZS 60898
Pollution degree	3
Tropicalisation	2 conforming to IEC 60068-1
Relative humidity	95 % at 55 °C
Height	81 mm
Width	18 mm
Depth	78.5 mm
Net weight	115 g

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.2 cm
Package 1 Width	1.8 cm
Package 1 Length	8.5 cm
Package 1 Weight	120.0 g

Offer Sustainability

Packaging without single use plastic	No
Packaging made with recycled cardboard	Yes
SCIP Number	F9865e0a-4be0-4110-b389-989cc9363cb0
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Halogen content performance	Halogen free product
Take-back	No