

Product data sheet

Characteristics

MCB6-150

Clipsal - Max 4, Miniature Circuit Breakers, C - Curve, 1 Pole, 1 Module, 240V, 50A, 6KA



Main

Product brand	Clipsal
---------------	---------

Complementary

Curve code	B
Number of poles	1
[In] rated current	50 A
Number of modules	1
[Ue] rated operational voltage	240 V
Breaking capacity	6 kA conforming to EN 60898
Network type	AC
Network frequency	50/60 Hz


Environment

IP degree of protection	IP20 conforming to IEC 60529
Ambient air temperature for operation	-5...40 °C
Standards	IEC 60898
Product certifications	CE: N17682[RETURN]ACMA: N11193[RETURN]RCM: N5400

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.2 cm
Package 1 Width	1.8 cm
Package 1 Length	8.5 cm
Package 1 Weight	118 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes

China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes