

Product data sheet

Characteristics

MD236D32

Acti9, MD Encapsulated distribution board,
Acti9, 36 poles, 250A main switch, 18mm,
IP56, grey



Main

Range	Acti9
Product name	Acti9 encapsulated DB
Device short name	MD
Product or component type	Distribution board
Device application	Distribution
Enclosure type	Weatherproof enclosure
Door type	External plain
Provided equipment	Earth/Neutral terminal block 165 A Pole filler Circuit schedule card Removable gland plates - top and bottom 2 keys Enclosure Door SAU chassis Main switch DIN rail
Colour	Grey

Complementary

[Ue] rated operational voltage	415 V
Network frequency	50 Hz
[Ie] rated operational current	250 A
Breaking capacity	25 kA
[Ui] rated insulation voltage	500 V
[Uimp] rated impulse withstand voltage	6 kV
Enclosure mounting	Surface
Poles description	3P + N
Enclosure material	Steel
Outgoer Pole capacity	36 x 18 mm
Enclosure material	steel
Height	1000 mm
Width	580 mm
Depth	225 mm
IP degree of protection	IP56

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	25 cm
Package 1 Width	60 cm
Package 1 Length	103 cm
Package 1 Weight	41 kg

Offer Sustainability

EU RoHS Directive	Not applicable, out of EU RoHS legal scope
-------------------	--