

## Product data sheet

### Characteristics

# MFINLINE-200

## Exhaust Fan, Airflow, Mixed Flow Inline, 200mm

### Main

Range of product	Mixed Flow Inline Fans
Range	Mixed Flow Inline Fans
Product brand	Clipsal
Product or component type	Exhaust fan
Noise level	52 dB
Provided equipment	Dowels User manual Screws 239 mm 295.5 mm 199 mm
Colour	Grey

### Complementary

Device mounting	Ceiling
Air flow	1040 m <sup>3</sup> /h
Pressure	345 Pa
Power consumption in W	108 W
[In] rated current	0.48 A
Maximum revolution speed	2620 rpm
Height	261 mm
[Ue] rated operational voltage	230 V AC
Material	Polypropylene

### Environment

IP degree of protection	IPx4
-------------------------	------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	29.7 cm
Package 1 Width	24.3 cm
Package 1 Length	30.5 cm
Package 1 Weight	4.213 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.