

Product data sheet

Characteristics

MX9E1212S

Clipsal MAX9, Switchboard Enclosure, Type 1, 2 Row, 24 Ways, Surface Mounted



Main

Range	MAX9
Product brand	Clipsal
Product or component type	Enclosure
Device application	Distribution
Number of 18 mm modules per row	12
Provided equipment	Earthing bar Neutral bar Circuit identification label Blanking plate
Colour	White electric (RAL 9003)
Door type	Plain door - reversible

Complementary

Enclosure mounting	Surface
Number of horizontal rows	2
[Ue] rated operational voltage	240/415 V AC
[In] rated current	100 A
[Ui] rated insulation voltage	500 V
Number of ways	24 ways
Cable entry	Knock-out cable entries
Type of rail	DIN
Enclosure material	Housing: plastic Front face: plastic
Width	345 mm
Height	424 mm
Depth	106 mm

Environment

Standards	AS/NZS 61439-3 AS/NZS 3000
Fire resistance	650 °C
IP degree of protection	IP30
IK degree of protection	IK05

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	13.0 cm
Package 1 Width	35.0 cm
Package 1 Length	43.0 cm
Package 1 Weight	4.174 kg
Unit Type of Package 2	CAR
Number of Units in Package 2	2

Package 2 Height	43.5 cm
Package 2 Width	29.0 cm
Package 2 Length	45.0 cm
Package 2 Weight	9.048 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	7-year
----------	--------