


## Product data sheet

### Characteristics

# MX9E2215F

Clipsal MAX9, Switchboard Enclosure, Type 2,  
2 Row, 30 Ways, Flush Mounted



### Main

Range	MAX9
Product brand	Clipsal
Product or component type	Enclosure
Device application	Distribution
Number of 18 mm modules per row	15
Provided equipment	Earthing bar Neutral bar Circuit identification label Blanking plate
Colour	White electric (RAL 9003)
Door type	Plain door - right and left

### Complementary

Enclosure mounting	Flush
Number of horizontal rows	2
[Ue] rated operational voltage	240/415 V AC
[In] rated current	100 A
[Ui] rated insulation voltage	500 V
Number of ways	30 ways
Cable entry	Knock-out cable entries
Type of rail	DIN
Enclosure material	Housing: plastic
Width	376 mm
Height	392 mm
Depth	104 mm

### Environment

Standards	AS/NZS 61439-3 AS/NZS 3000
Fire resistance	650 °C
IP degree of protection	IP40
IK degree of protection	IK05

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10.8 cm
Package 1 Width	38.4 cm
Package 1 Length	41.4 cm
Package 1 Weight	2.936 kg
Unit Type of Package 2	P12
Number of Units in Package 2	72

Package 2 Height	165.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	226.392 kg

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#"> REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China RoHS Regulation	<a href="#"> China RoHS Declaration</a>
RoHS exemption information	<a href="#"> Yes</a>
Environmental Disclosure	<a href="#"> Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

### Contractual warranty

Warranty	7-year
----------	--------