

Product data sheet

Characteristics

MX9E3318S

Switchboard Enclosure, MAX9, type 3, 3 row,
54 ways, Surface mounted



Main

Range	MAX9
Product brand	Clipsal
Product or component type	Enclosure
Device application	Distribution
Number of 18 mm modules per row	18
Provided equipment	Earthing bar Neutral bar Circuit identification label Blanking plate
Colour	White electric (RAL 9003)
Door type	Plain door - reversible

Complementary

Enclosure mounting	Surface
Number of horizontal rows	3
[Ue] rated operational voltage	240/415 V AC
[In] rated current	100 A
[Ui] rated insulation voltage	500 V
Number of ways	54 ways
Cable entry	Knock-out cable entries
Type of rail	DIN
Enclosure material	Housing: plastic
Width	426 mm
Height	600 mm
Depth	145 mm

Environment

Standards	AS/NZS 61439-3 AS/NZS 3000
Fire resistance	650 °C
IP degree of protection	IP40
IK degree of protection	IK09

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	3.9 kg
Package 1 Height	51 cm
Package 1 width	13.5 cm
Package 1 Length	68 cm
Unit Type of Package 2	P12
Number of Units in Package 2	18
Package 2 Weight	93.9 kg
Package 2 Height	120 cm

Package 2 width	80 cm
Package 2 Length	120 cm

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration