

## Product data sheet

### Characteristics

# MX9MS1100

Clipsal MAX9, Isolator Switch, 1P, 100A, 240V



### Main

Range	MAX9
Product or component type	Switch disconnecter
Device application	Switch
Poles description	1P
Utilisation category	AC-22A
Suitability for isolation	Yes

### Complementary

[Ie] rated operational current	AC-22A: 100 A at 240 V AC 50/60 Hz
[Ue] rated operational voltage	240 V AC 50/60 Hz
Network frequency	50/60 Hz
[Icm] rated short-circuit making capacity	5 kA 240 V AC at 50/60 Hz
[Icw] rated short-time withstand current	1500 A during 1 s conforming to IEC 60947-3 at 240 V
[Ith] conventional free air thermal current	100 A
Maximum power	AC-22A: 4.7 W at 240 V AC 50/60 Hz
[Ui] rated insulation voltage	500 V AC 50/60 Hz
[Uimp] rated impulse withstand voltage	6 kV
Control type	Toggle
Local signalling	ON/OFF indication
Contact position indicator	Yes
Mounting mode	Clip-on
Mounting support	DIN rail
Comb busbar and distribution block compatibility	Top or bottom: YES
9 mm pitches	2
Height	85 mm
Width	18 mm
Depth	75 mm
Net weight	81 g
Colour	White
Mechanical durability	20000 cycles
Electrical durability	AC-22A: 10000 cycles 240 V AC 50/60 Hz
Connections - terminals	Tunnel type terminals (top or bottom) - 6...50 mm <sup>2</sup> - rigid Tunnel type terminals (top or bottom) - 6...35 mm <sup>2</sup> - flexible
Wire stripping length	14 mm
Tightening torque	3.5 N.m

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.





## Environment

Standards	IEC 60947-3
Quality labels	RCM
IP degree of protection	IP20
Pollution degree	3
Overvoltage category	IV
Tropicalisation	Severity B conforming to IEC 60068-2-30
Relative humidity	95 % at 55 °C
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...85 °C

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.5 cm
Package 1 Width	7.5 cm
Package 1 Length	1.8 cm
Package 1 Weight	80 g

## Offer Sustainability

REACH Regulation	 <a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 <a href="#">Yes</a>

## Contractual warranty

Warranty	7-year
----------	--------