


Product data sheet

Characteristics

LX4D7BW

TeSys; TeSys Deca, contactor coil, LX4D7, 24 V DC wide range for 80 A contactor



Main

Range	TeSys
Product or component type	Contactor coil
Device short name	LX4D7
Control circuit type	DC wide range
[Uc] control circuit voltage	24 V DC
Average resistance	23.5 Ohm at 20 °C
Inductance of closed circuit	1.75 H
Product compatibility	LC1D80
Mechanical durability	10 Mcycles
Maximum operating rate	3600 cyc/h 60 °C

Complementary

Coil technology	Without built-in suppressor module
Control circuit voltage limits	Drop-out: 0.1...0.3 Uc (at <55 °C) Operational: 0.75...1.2 Uc (at <55 °C)
Time constant	75 ms
Inrush power in W	22 W (at 20 °C)
Hold-in power consumption in W	22 W at 20 °C

Environment

Ambient air temperature for operation	-5...60 °C
Net weight	0.68 kg

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9 cm
Package 1 Width	11.5 cm
Package 1 Length	14.5 cm
Package 1 Weight	680 g

Contractual warranty

Warranty	18 months
----------	-----------