

Product data sheet

Characteristics

NSYADR200

One asymmetric mounting rail, Spacial CRN, 32x15 L 2000mm, Order by Multiples of 10 units

Main

Anwendung	Multi-purpose
Range	PanelSeT
Product or component type	Rail
Accessory / separate part category	Mounting accessory
Type of rail	Asymmetrical DIN rail
Enclosure nominal dimensions	-
Range compatibility	PanelSeT Thalassa
Device composition	1 rail
Quantity per set	Set of 10

Complementary

Material	Galvanised steel
Surface finish	Not perforated
Fixing mode	By fixing element - structure of enclosure location
Adjustment	Continuous adjustment Pitch 25 mm
Length	2000 mm
Height	Nominal: 15 mm
Width	Nominal: 32 mm
Thickness	1.5 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	15.0 cm
Package 1 Width	32.0 cm
Package 1 Length	2000.0 cm
Package 1 Weight	1.45 kg
Unit Type of Package 2	CAR
Number of Units in Package 2	20
Package 2 Height	7.6 cm
Package 2 Width	9.0 cm
Package 2 Length	201.0 cm
Package 2 Weight	29.0 kg
Unit Type of Package 3	PAL
Number of Units in Package 3	600
Package 3 Height	50.0 cm
Package 3 Width	200.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	870.0 kg

Offer Sustainability

Packaging without single use plastic	No
Packaging made with recycled cardboard	No
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
Take-back	No

Contractual warranty

Warranty	18 months
----------	-----------