

Product data sheet

Characteristics

NSYDLM84

Spacial, Modular chassis DLM type for
SPACIAL WM enclosure, 84 modules,
H800xW600mm



Main

Range	Spacial
Accessory / separate part category	Mounting accessory
Application	Modular distribution application Multi-purpose
Product or component type	Chassis
Device short name	DLM
For enclosure nominal dimensions	-
Mounting location	Front of enclosure Step slide
Range compatibility	Spacial Spacial S3D Spacial Spacial S3X Spacial Spacial CRN
Device composition	1 chassis structure 2 finish cover 1 neutral/earth strip 2 x 16 mm ² 5 x 6 mm ² 3 front panels with 35 mm DIN rail 1 plain front panel with mounting plate
Quantity per set	Set of 1

Complementary

Material	Steel
Colour	Front panel: grey (RAL 7035)
Surface finish	Polyester powder
Fixing mode	By fixing element - on front and back with supports location
Adjustment	In height from 40 to 85 mm for DIN rail
Number of horizontal rows	3
Total number of 18 mm modules	84
Type of front plate	Plain and cut-out plates
Number of cut-out	3 cut-outs
Height	753 mm
Width	555 mm
Depth	101.5 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11.500 cm
Package 1 Width	56.000 cm
Package 1 Length	77.000 cm
Package 1 Weight	8.465 kg
Unit Type of Package 2	P12
Number of Units in Package 2	12

Package 2 Height	90.000 cm
Package 2 Width	80.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	113.580 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------