

Product data sheet

Characteristics

NSYTRAL210

Linery, Plug-in bridge, Linergy TR, 10 points, for 2.5mm² terminal blocks, red, 10 way, set of 10



Main

Range	Linery
Product name	Linery TR
Product or component type	Plug-in bridge
Device short name	TRA
Accessory / separate part category	Connection accessory
Product compatibility	TRV screw terminal terminal block[RETURN]TRP push-in terminal block[RETURN]TRR spring terminal terminal block[RETURN]TRH IDC terminal block
Number of ways	10 ways

Complementary





Cable cross section	2.5 mm ²
Number of connections	2 3 4
Number of measurement input	3 1 2 4 6
Quantity per set	Set of 10
Net weight	9 g
Colour	Red

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.0 cm
Package 1 Width	15.0 cm
Package 1 Length	17.0 cm
Package 1 Weight	8.0 g
Unit Type of Package 2	BAG
Number of Units in Package 2	10
Package 2 Height	15.0 cm
Package 2 Width	5.0 cm
Package 2 Length	17.0 cm
Package 2 Weight	88.0 g
Unit Type of Package 3	S02
Number of Units in Package 3	800
Package 3 Height	15.0 cm
Package 3 Width	30.0 cm

Package 3 Length	40.0 cm
Package 3 Weight	7.352 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Circularity Profile	No need of specific recycling operations
Halogen content performance	Halogen free plastic parts product

Contractual warranty

Warranty	18 months
----------	-----------