


## Product data sheet

### Characteristics

# NSYTRR162

Linery, Terminal block, Linery TR, spring type, feed through, 2 points, 16mm<sup>2</sup>, grey



#### Main

Range	Linery
Product name	Linery TR
Product or component type	Terminal block
Device short name	TRR
Accessory / separate part categor	Connection accessory
Terminal block type	Passthrough
Terminal block level	1
Mounting mode	Clip-on
Nominal cross section	16 mm <sup>2</sup>
Length	80 mm
Colour	Grey
Quantity per set	Set of 50

#### Complementary

Width	12.2 mm
Height	51 mm
Connections - terminals	1 x spring terminal: upstream 1 x spring terminal: downstream
Number of connections	2
Connection position	Top
Number of measurement input	2
Cable cross section	0.2...16 Mm <sup>2</sup> , flexible without cable end 0.2...25 Mm <sup>2</sup> , solid with cable end 1.5...16 Mm <sup>2</sup> , flexible with cable end 0.2...25 mm <sup>2</sup> , solid without cable end
Wire stripping length	18 mm
Tool type	Connection: flat screwdriver Disconnection: flat screwdriver
[Ue] rated operational voltage	600 V CSA[RETURN]800 V conforming to EN/IEC 60947-7-1[RETURN]600 V cURus
[In] rated current	76 A conforming to EN/IEC 60947-7-1 85 A CSA 85 A cURus
Material	Polyamide 6/6: insulating case Copper alloy: connector and screw Copper alloy: commoning link Chromium-nickel steel: spring
Dielectric loss	0.01 at 1 MHz conforming to IEC 60250 0.01 at 1 MHz conforming to VDE 0303-T4
Dielectric constant	3.7 at 1 MHz
Resistivity	10000 MΩ.M conforming to IEC 60093 10000 MΩ.m conforming to VDE 0303-T30
Surface resistance	1000 GΩ conforming to IEC 60093 1000 GΩ conforming to VDE 0303-T30
Creep resistance	500 CTI (> 400 kV) conforming to IEC 60093 500 CTI (> 400 kV) conforming to VDE 0303-T30

Flame retardance	V0, thickness 0.8 mm conforming to UL 94
Net weight	37 g
Range compatibility	Prisma G Prisma P Prisma PH Prisma Pack Spacial Kaedra Pragma TeSys
Product compatibility	Spacial enclosures

## Environment

Product certifications	EAC[RETURN]GL[RETURN]IEC-Ex[RETURN]DNV[RETURN]VDE[RETURN]CSA[RETURN]cURus[RETURN]ATEX[RETURN]LR
Dielectric strength	1000 V conforming to IEC 60243-1
Ambient air temperature for operation	-40...130 °C conforming to IEC 60216-1 -40...130 °C conforming to VDE 0304-T21

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.500 cm
Package 1 Width	11.500 cm
Package 1 Length	36.000 cm
Package 1 Weight	37.000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	50
Package 2 Height	9.500 cm
Package 2 Width	11.500 cm
Package 2 Length	36.000 cm
Package 2 Weight	1.899 kg
Unit Type of Package 3	S03
Number of Units in Package 3	300
Package 3 Height	30.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	11.932 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
Halogen content performance	Halogen free plastic parts product

## Contractual warranty

Warranty	18 months
----------	-----------