

Product data sheet

Characteristics

MB272EH0

Acti9, MB Encapsulated distribution board,
Acti9, 72 poles, 250A no main switch,
18/27mm, IP42, grey



Main

Range	Acti9
Product name	Acti9 encapsulated DB
Device short name	MB
Product or component type	Distribution board
Device application	Distribution
Enclosure type	Standard
Door type	External plain
Provided equipment	Pole filler Circuit schedule card Enclosure Door Removable gland plates Keys SAU chassis 2 earth/neutral terminal block - top and bottom 165 A DIN rail
Colour	Grey

Complementary

[Ue] rated operational voltage	415 V
Network frequency	50 Hz
[Ie] rated operational current	250 A
Breaking capacity	25 kA
[Ui] rated insulation voltage	500 V
[Uimp] rated impulse withstand voltage	6 kV
Enclosure mounting	Surface
Poles description	3P + N
Enclosure material	Steel
Outgoer Pole capacity	60 x 18 mm 12 x 27 mm
Enclosure material	steel
Height	1200 mm
Width	580 mm
Depth	235 mm
IP degree of protection	IP42

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	25 cm
Package 1 Width	60 cm
Package 1 Length	121 cm
Package 1 Weight	41 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.