

Product data sheet

Characteristics

MFINLINE-100

Clipsal, Exhaust Fan, Mixed Flow Inline, 100mm



Main

Range of product	Mixed Flow Inline Fans
Range	Mixed Flow Inline Fans
Product brand	Clipsal
Product or component type	Exhaust fan
Noise level	32 dB
Provided equipment	Screws 195.8 mm 302.5 mm 97 mm Dowels User manual
Colour	Grey

Complementary

Device mounting	Ceiling
Air flow	245 m ³ /h
Pressure	154 Pa
Power consumption in W	25 W
[In] rated current	0.11 A
Maximum revolution speed	2620 rpm
Height	226 mm
[Ue] rated operational voltage	230 V AC
Material	Polypropylene

Environment

IP degree of protection	IPx4
-------------------------	------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	24.7 cm
Package 1 Width	20.7 cm
Package 1 Length	31.2 cm
Package 1 Weight	2.4 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration

RoHS exemption information

 [Yes](#)

Environmental Disclosure

 [Product Environmental Profile](#)
