

## Product data sheet

### Characteristics

# ML2031VRCD10-WE

Residual Current Circuit Breaker, Medilec, 2 Pole, 20A, 10mA, 250V, Vertical

### Main

Product or component type	Residual current device
Product brand	Clipsal
Poles description	2P
[In] rated current	20 A
Earth-leakage sensitivity	10 mA
Earth-leakage protection class	Type I

### Complementary

[Ue] rated operational voltage	250 V AC
Size	116 x 76 mm conforming to DIN 43880
Colour	White electric

### Environment

Standards	AS/NZS 3190
-----------	-------------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7 cm
Package 1 Width	9.4 cm
Package 1 Length	11.7 cm
Package 1 Weight	180 g

### Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.