

## Product data sheet

### Characteristics

# P3041A-BK

## Pro Series, switch, architrave, vertical, 1 or 2 way, 10 AX, Black



### Main

Range	Pro Series
Product or component type	Switch
Colour tint	Black
Type of packing	Polybag
Quantity per set	Set of 10

### Complementary

Device presentation	Complete product
Control type	Rocker
Device mounting	Wall
Installation direction	Vertical
Switch function	1-pole 1/2-way
Number of rocker	1
Rated current	20 A/16 AX
[Ue] rated operational voltage	250 V
Material	PC (polycarbonate) PP (polypropylene) ABS (acrylonitrile butadiene-styrene) POM (polyoxymethylene)
Fixing mode	By screws
Surface finish	Glossy
Surface treatment	Untreated
Connections - terminals	Screw terminal
Clamping connection capacity	1 x 1.5...4 x 1.5 mm <sup>2</sup> for rigid or stranded cable(s) 3 x 2.5 mm <sup>2</sup> for stranded cable(s) 1 x 4 mm <sup>2</sup> for stranded cable(s)
Height	113 mm
Width	38 mm
Depth	40 mm
Net weight	0.046 kg

### Environment

Ambient air temperature for operation	0...45 °C
Relative humidity	10...95 %
Product certifications	RCM

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	52.33 g
Package 1 Height	3.8 cm
Package 1 width	7.8 cm
Package 1 Length	11.6 cm