

## Product data sheet

### Characteristics

# P3HS900AL-WE

Airflow, Ceiling Sweep Fan 3 Aluminium Blades  
900mm



### Main

Range	Clipsal
Product brand	Clipsal
Device short name	sweep fan
Product or component type	Fan
Product destination	Ceiling fan
Device application	Residential Commercial


### Complementary

Provided equipment	Fan 900 mm
[Ue] rated operational voltage	240 V AC 50 Hz
Material	Aluminium
Air flow	8340 m3/h
Power consumption in W	60 W
Maximum revolution speed	375 rpm

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	24.5 cm
Package 1 Width	26.5 cm
Package 1 Length	41.5 cm
Package 1 Weight	5.5 kg

### Offer Sustainability

REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 Yes

### Contractual warranty

Warranty	3 Years
----------	---------