

Product data sheet

Characteristics

RCBE220/30S

RCBO SLIM, Clipsal Resi MAX, 1PN 20A C curve 30mA Type A 4500A



Main

Range	Resi MAX
Product or component type	Residual current breaker with overcurrent protection (RCBO)
Product brand	Clipsal
Device application	Distribution
Poles description	1P + N
Neutral position	Left
Number of modules	1
Number of protected poles	1
[In] rated current	20 A
Network type	AC
Trip unit technology	Thermal-magnetic
Curve code	C
Earth-leakage sensitivity	30 mA
Earth-leakage protection class	Type A
Breaking capacity	4.5 kA

Complementary

[Ue] rated operational voltage	240 V AC
Control type	ON/OFF locking with trip free mechanism
Local signalling	ON/OFF indication
Mounting mode	Clip-on
Mounting support	DIN rail
Size	92.5 x 18 x 71.5 mm conforming to DIN 43880

Environment

Standards	AS/NZS 61009
IP degree of protection	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.8 cm
Package 1 Width	10.2 cm
Package 1 Length	2.3 cm
Package 1 Weight	141 g
Unit Type of Package 2	CAR
Number of Units in Package 2	72
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	10.584 kg

Unit Type of Package 3	PAL
Number of Units in Package 3	864
Package 3 Height	125 cm
Package 3 Width	60 cm
Package 3 Length	80 cm
Package 3 Weight	127.008 kg

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes