

## Product data sheet

### Characteristics

# RCBE232/30S

## Clipsal Resi MAX, RCBO SLIM 1PN 32A C curve 30mA Type A 4500A



### Main

Range	Resi MAX
Product or component type	Residual current breaker with overcurrent protection (RCBO)
Product brand	Clipsal
Device application	Distribution
Poles description	1P + N
Neutral position	Left
Number of modules	1
Number of protected poles	1
[In] rated current	32 A
Network type	AC
Trip unit technology	Thermal-magnetic
Curve code	C
Earth-leakage sensitivity	30 mA
Earth-leakage protection class	Type A
Breaking capacity	4.5 kA

### Complementary

[Ue] rated operational voltage	240 V AC
Control type	ON/OFF locking with trip free mechanism
Local signalling	ON/OFF indication
Mounting mode	Clip-on
Mounting support	DIN rail
Size	92.5 x 18 x 71.5 mm conforming to DIN 43880

### Environment

Standards	AS/NZS 61009
IP degree of protection	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7 cm
Package 1 Width	2 cm
Package 1 Length	9.8 cm
Package 1 Weight	146 g
Unit Type of Package 2	CAR
Number of Units in Package 2	72
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm

Package 2 Weight	10.584 kg
Unit Type of Package 3	PAL
Number of Units in Package 3	864
Package 3 Height	125 cm
Package 3 Width	60 cm
Package 3 Length	80 cm
Package 3 Weight	127.008 kg

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>