

Product data sheet

Characteristics

MX9B124P

Clipsal MAX9, Pin Type Comb Busbar, 1P, 100 A, 24 Modules



Main

Product brand	Clipsal
Range	MAX9
Product or component type	Comb busbar
Total number of 18 mm modules	24

Complementary

Number of ways	24 ways L
Poles configuration	24 x 1P
Connection pitch	18 mm
Insulation	Insulated
Device presentation	Cuttable
Provided components	2 end-pieces Tooth covers
[Ie] rated operational current	100 A
[Ue] rated operational voltage	230 V AC
[Ui] rated insulation voltage	500 V
[Uimp] rated impulse withstand voltage	6 kV
Mounting mode	Horizontal
Mounting location	Top
Height	17 mm
Width	423 mm
Depth	15 mm
Colour	Grey (RAL 9003)

Environment

Standards	AS/NZS 61439-3 AS/NZS 3000
Fire resistance	960 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.4 cm
Package 1 Width	2.1 cm
Package 1 Length	42.7 cm
Package 1 Weight	106.0 g
Unit Type of Package 2	CAR

Number of Units in Package 2	50
Package 2 Height	9.5 cm
Package 2 Width	10.5 cm
Package 2 Length	103.0 cm
Package 2 Weight	5.3 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	7-year
----------	--------