


Product data sheet

Characteristics

RMXE112S

Consumer switchboard, Clipsal Resi MAX, 1 row 12 modules Surface Mounted



Main

Range	Resi MAX
Product brand	Clipsal
Product or component type	Enclosure
Enclosure type	Mini enclosure for modular device
Device application	Distribution
Number of 18 mm modules per row	12
Provided equipment	DIN rail Earth terminal block Neutral terminal block
Type of front cover	Plain
Colour	White (RAL 9003)
Door type	Plain door

Complementary

Enclosure mounting	Surface
Number of horizontal rows	1
[In] rated current	63 A
Number of ways	12 ways
Cable entry	Knock-out top and bottom Knock-out rear
Type of rail	35 mm asymmetrical rail
Number of terminal blocks	12 earth (screw connection) 14 neutral (screw connection)
Enclosure material	Technoplastic
Width	268 mm external
Height	228 mm external
Depth	101.5 mm external

Environment

Fire resistance	650 °C
IP degree of protection	IP40
IK degree of protection	IK07

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11.2 cm
Package 1 Width	29.0 cm
Package 1 Length	27.0 cm
Package 1 Weight	0.9 kg
Unit Type of Package 2	P12
Number of Units in Package 2	90

Package 2 Height	80.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	93.0 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations