


Product data sheet

Characteristics

RMXE118F

Clipsal Resi MAX, Consumer switchboard 1 row 18 modules Flush Mounted



Main

Range	Resi MAX
Product brand	Clipsal
Product or component type	Enclosure
Enclosure type	Mini enclosure for modular device
Device application	Distribution
Number of 18 mm modules per row	18
Provided equipment	DIN rail Earth terminal block Neutral terminal block
Type of front cover	Plain
Colour	White (RAL 9003)
Door type	Plain door

Complementary

Enclosure mounting	Flush
Number of horizontal rows	1
[In] rated current	63 A
Number of ways	18 ways
Cable entry	Knock-out top and bottom Knock-out rear
Type of rail	35 mm asymmetrical rail
Number of terminal blocks	18 earth (screw connection) 22 neutral (screw connection)
Enclosure material	Technoplastic
Width	378 Mm external 402 mm (with door)
Height	228 Mm external 252 mm (with door)
Depth	80 Mm external 98 mm (with door)

Environment

Fire resistance	Door: 650 °C Back box: 850 °C
IP degree of protection	IP40
IK degree of protection	IK07

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10.5 cm
Package 1 Width	27.0 cm
Package 1 Length	41.0 cm
Package 1 Weight	1.2 kg
Unit Type of Package 2	P12

Number of Units in Package 2	60
Package 2 Height	80.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	84.0 kg

Offer Sustainability

EU RoHS Directive	Not applicable, out of EU RoHS legal scope
-------------------	--