

## Product data sheet

### Characteristics

# RPSW110M

Rowco, IP30, 2 Way, 250V, 10A, 1 Pole



### Main

Range of product	PDL
Product brand	Clipsal
Device presentation	Basic element

### Complementary

Switch function	1-pole
Number of poles	1
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	10 A
Marking	Without marking

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.7 cm
Package 1 Width	6.7 cm
Package 1 Length	12.5 cm
Package 1 Weight	364.0 g

### Offer Sustainability

EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Circularity Profile	No need of specific recycling operations