

Product data sheet

Characteristics

MX9RC240

Residual Current Circuit Breaker (RCCB), MAX9, 2P, 40A, 30mA, A Type



Main

Range	MAX9
Product or component type	Residual current circuit breaker (RCCB)
Poles description	2P
[In] rated current	40 A conforming to AS/NZS 61008.1
Network type	AC
Network frequency	50 Hz
Earth-leakage sensitivity	30 mA
[Ue] rated operational voltage	240 V

Complementary

Earth-leakage protection time delay	Instantaneous
Earth-leakage protection class	Type A
Rated breaking and making capacity	Im 500 A at 240 V AC 50 Hz conforming to AS/NZS 61008.1
Rated conditional short-circuit current	MAX9 MCB: Inc 6 kA 40 A
[Ui] rated insulation voltage	440 V AC 50 Hz conforming to AS/NZS 61008.1
[Uimp] rated impulse withstand voltage	4 kV
Surge current	250 A
Control type	Toggle
Local signalling	ON/OFF indication
Mounting mode	Clip-on
Mounting support	DIN rail
Standards	IEC 61008-2-1 EN/IEC 61008-1
Quality labels	RCM
9 mm pitches	4
Height	85 mm
Width	36 mm
Depth	75 mm
Net weight	210 g
Colour	White (RAL 9003)
Mechanical durability	10000 cycles
Electrical durability	4000 cycles AC 50 Hz
Connections - terminals	Tunnel type terminals (top or bottom)
Wire stripping length	14 mm for top or bottom connection
Tightening torque	3.5 N.m top or bottom
Temperature derating table	40 °C (40 A) 45 °C (37.5 A) 50 °C (35 A) 55 °C (32.5 A) 60 °C (30 A) 65 °C (27.5 A) 70 °C (25 A)
Grid distance	35 mm

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environment

IP degree of protection	IP20
Pollution degree	2
Overvoltage category	III
Relative humidity	95 % at 55 °C
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...85 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8 cm
Package 1 Width	9 cm
Package 1 Length	4 cm
Package 1 Weight	214 g
Unit Type of Package 2	BB1
Number of Units in Package 2	6
Package 2 Height	9 cm
Package 2 Width	25.4 cm
Package 2 Length	10.6 cm
Package 2 Weight	1.386 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	7-year
----------	--------