

Product data sheet

Characteristics

MX9SP140

Clipsal MAX9, Surge Protection Device, SPD,
1P, 40kA



Main

Range	MAX9
Product or component type	Surge arrester
Poles description	1P
Remote signalling	With
Signal contacts composition	1 NO + 1 NC
Surge arrester type	Electrical distribution network
Earthing system	TN-C TN-S TT
Device application	Distribution

Complementary

Surge arrester class type	Type 2
Surge arrester technology	MOV
Local signalling	Flag
[Ue] rated operational voltage	240 V +/- 6 % AC 50/60 Hz
Nominal discharge current	15 kA conforming to IEC 61643-11
Maximum discharge current	40 kA conforming to IEC 61643-11
[Uc] maximum continuous operating voltage	350 V AC
Maximum [Up] voltage protection level	<1.6 kV type 2
[Ures] residual voltage	1545 V
[Ut] temporary overvoltage	336 V L/PE 5 s withstand
Local signalling	White/red flag
Local signalling	Flag (white/red)
Signalling circuit voltage	AC: 250 V 50/60 Hz
Signalling output current	0.25 A
Mounting mode	Clip-on
Mounting support	DIN rail
Comb busbar and distribution block compatibility	Tooth
9 mm pitches	2
Height	85 mm
Width	18 mm
Depth	64 mm
Net weight	119 g
Colour	White (RAL 9003)
Cable cross section	2.5...25 Mm ² rigid 4...16 mm ² flexible
Response time	<= 25 ns
Maximum residual current	0.6 mA 240 V
Connections - terminals	Tunnel type terminal (top or bottom) 2.5...25 mm ² rigid Tunnel type terminal (top or bottom) 4...16 mm ² flexible
Wire stripping length	14 mm
Tightening torque	3.5 N.m





Environment

Standards	IEC 61643-11:2011 EN 61643-11:2012
Quality labels	RCM
IP degree of protection	IP20
IK degree of protection	IK03 conforming to IEC 62262
Pollution degree	2
Relative humidity	5...95 % at 55 °C
Operating altitude	0...2000 m
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...85 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.5 cm
Package 1 Width	2.5 cm
Package 1 Length	9.5 cm
Package 1 Weight	132 g

Offer Sustainability

REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes

Contractual warranty

Warranty	7-year
----------	--------