

Product data sheet

Characteristics

NSYDLM48

Spacial, Modular chassis DLM type for SPACIAL WM enclosure, 48 modules, H500xW400mm



Main

Range	Spacial
Accessory / separate part category	Mounting accessory
Application	Multi-purpose Modular distribution application
Product or component type	Chassis
Device short name	DLM
For enclosure nominal dimensions	-
Mounting location	Step slide Front of enclosure
Range compatibility	Spacial Spacial S3D Spacial Spacial S3X Spacial Spacial CRN
Device composition	1 chassis structure 2 finish cover 1 neutral/earth strip 2 x 16 mm ² 5 x 6 mm ² 3 front panels with 35 mm DIN rail
Quantity per set	Set of 1

Complementary

Material	Steel
Colour	Front panel: grey (RAL 7035)
Surface finish	Polyester powder
Fixing mode	By fixing element - on front and back with supports location
Adjustment	In height from 40 to 85 mm for DIN rail
Number of horizontal rows	3
Total number of 18 mm modules	48
Type of front plate	Plain and cut-out plates
Number of cut-out	3 cut-outs
Height	453 mm
Width	355 mm
Depth	101.5 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11.000 cm
Package 1 Width	36.500 cm
Package 1 Length	46.500 cm
Package 1 Weight	3.654 kg
Unit Type of Package 2	S04
Number of Units in Package 2	2
Package 2 Height	30 cm

Package 2 Width	40 cm
Package 2 Length	60 cm
Package 2 Weight	7.958 kg
Unit Type of Package 3	P12
Number of Units in Package 3	16
Package 3 Height	90.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	75.664 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------