

Product data sheet

Characteristics

SAU25060183DF

SAU Chassis, Acti9, 250A, 3Ph, 60 poles,
18mm for iC60 MCB and RCBO, dual feed



Main

Range	Acti9
Product or component type	Chassis
Device application	Distribution

Complementary

Range compatibility	Acti 9 distribution board
Network type	AC
[In] rated current	250 A
Number of ways	1 way (incomer) - 3P
Rated voltage	415 V 50 Hz
Short-circuit withstand	25 kA 0.1 s
[Ui] rated insulation voltage	500 V
[Uimp] rated impulse withstand voltage	6 kV
Number of poles	60
Number of poles	60 x 18 mm
Width	215 mm
Length	542 mm
Busbar pitch	18 mm
Location of connection	Dual feed

Environment

Standards	AS/NZS 61439
-----------	--------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.5 cm
Package 1 Width	24.5 cm
Package 1 Length	82.6 cm
Package 1 Weight	4.8 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes