

Product data sheet

Characteristics

SAU250H123DF

SAU hybrid Chassis, Acti9, 250A, 3Ph, 6 poles 12mm and 6 poles 27mm for MCB and RCBO, dual feed



Main

Range	Acti9
Product or component type	Chassis
Device application	Distribution

Complementary

Range compatibility	Acti 9 distribution board
Network type	AC
[In] rated current	250 A
Number of ways	1 way (incomer) - 3P
Rated voltage	415 V 50 Hz
Short-circuit withstand	25 kA 0.1 s
[Ui] rated insulation voltage	500 V
[Uimp] rated impulse withstand voltage	6 kV
Number of poles	12
Number of poles	6 x 18 mm 6 x 27 mm
Width	215 mm
Length	137 mm
Busbar pitch	18 Mm 27 mm
Location of connection	Dual feed

Environment

Standards	AS/NZS 61439
-----------	--------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.5 cm
Package 1 Width	42 cm
Package 1 Length	24.4 cm
Package 1 Weight	1987 g

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes