

## Product data sheet

### Characteristics

# NSYDLP297G

Thalassa, DLP modular dist chassis  
 297modules(18mm) insulating material for PLA  
 H1500xW750



### Main

Range	Thalassa
Accessory / separate part category	Mounting accessory
Application	Multi-purpose Modular distribution application
Product or component type	Chassis
Device short name	DLP
For enclosure nominal dimensions	-
Mounting location	Front of enclosure
Range compatibility	Thalassa (Thalassa PLA) Thalassa (Thalassa PHD)
Device composition	1 chassis structure 1 neutral/earth strip 2 x 16 mm <sup>2</sup> 5 x 6 mm <sup>2</sup> 9 front panels with 35 mm DIN rail
Additional information	IP2x not respected when chassis is mounted at 67 mm

### Complementary

Material	Front panel: self-extinguishing Chassis structure and rails: galvanised steel
Colour	Front panel: grey (RAL 7035)
Fixing mode	By fixing element - on front with supports location
Adjustment	In height from 40 to 85 mm for DIN rail
Number of horizontal rows	9
Total number of 18 mm modules	297
Type of front plate	Cut-out plate
Number of cut-out	9 cut-outs
Height	1500 mm
Width	750 mm

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	14.000 cm
Package 1 Width	67.000 cm
Package 1 Length	143.000 cm
Package 1 Weight	12.520 kg
Unit Type of Package 2	P2M
Number of Units in Package 2	4
Package 2 Height	90.000 cm
Package 2 Width	200.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	65.080 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>