


Product data sheet

Characteristics

NSYPAPLA157G

Thalassa, Internal door for PLA enclosure
H1500xW750 mm



Main

Range	Thalassa
Accessory / separate part category	Enclosure accessory
Product or component type	Door
Application	Multi-purpose
For enclosure nominal dimensions	-
Mounting location	Front side
Range compatibility	Thalassa (Thalassa PLA)
Device composition	1 door Fixing elements M8 brass inserts

Complementary

Material	Aluminium
Colour	Grey (RAL 7035)
Lock type	Lock 5 mm double bar
Number of locks	2
Door type	Internal plain
Door opening side	Left (110 °)
Height	1398 mm
Width	648 mm
Depth	30 mm available depth between enclosure door:

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.000 cm
Package 1 Width	65.500 cm
Package 1 Length	141.000 cm
Package 1 Weight	7.800 kg
Unit Type of Package 2	P2M
Number of Units in Package 2	30
Package 2 Height	45.000 cm
Package 2 Width	200.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	249.000 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile