

Product data sheet

Characteristics

SAU250H183DF

SAU hybrid Chassis, Acti9, 250A, 3Ph, 12 poles 18mm and 6 poles 27mm for MCB and RCBO, dual feed

Main

| | |
|---------------------------|--------------|
| Range | Acti9 |
| Product or component type | Chassis |
| Device application | Distribution |

Complementary

| | |
|--|---------------------------|
| Range compatibility | Acti 9 distribution board |
| Network type | AC |
| [In] rated current | 250 A |
| Number of ways | 1 way (incomer) - 3P |
| Rated voltage | 415 V 50 Hz |
| Short-circuit withstand | 25 kA 0.1 s |
| [Ui] rated insulation voltage | 500 V |
| [Uimp] rated impulse withstand voltage | 6 kV |
| Number of poles | 18 |
| Number of poles | 12 x 18 mm 6 x 27 mm |
| Width | 215 mm |
| Length | 191 mm |
| Busbar pitch | 18 Mm 27 mm |
| Location of connection | Dual feed |

Environment

| | |
|-----------|--------------|
| Standards | AS/NZS 61439 |
|-----------|--------------|

Packing Units

| | |
|------------------------------|---------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 9.5 cm |
| Package 1 Width | 47 cm |
| Package 1 Length | 24.8 cm |
| Package 1 Weight | 2382 g |

Offer Sustainability

| | |
|----------------------------|--|
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration |
| Mercury free | Yes |
| China RoHS Regulation |  China RoHS Declaration |
| RoHS exemption information |  Yes |