

Product data sheet

Characteristics

SAU250H963DF

SAU hybrid Chassis, Acti9, 250A, 3Ph, 84 poles 18mm and 12 poles 27mm for MCB and RCBO, dual feed

Main

Range	Acti9
Product or component type	Chassis
Device application	Distribution

Complementary

Range compatibility	Acti 9 distribution board
Network type	AC
[In] rated current	250 A
Number of ways	1 way (incomer) - 3P
Rated voltage	415 V 50 Hz
Short-circuit withstand	25 kA 0.1 s
[Ui] rated insulation voltage	500 V
[Uimp] rated impulse withstand voltage	6 kV
Number of poles	96
Number of poles	12 x 27 mm 84 x 18 mm
Width	215 mm
Length	920 mm
Busbar pitch	27 Mm 18 mm
Location of connection	Dual feed

Environment

Standards	AS/NZS 61439
-----------	--------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.5 cm
Package 1 Width	24.5 cm
Package 1 Length	120.4 cm
Package 1 Weight	7.5 kg