


Product data sheet

Characteristics

NSYTBP191610HT

Thalassa, PC box IP66 IK08 RAL7035
 Int.H175W150D100 Ext.H193W164D105
 Transp.cover H40



Main

Range	Thalassa
Product name	Thalassa TBP
Device application	Multi-purpose
Category	Industrial box
Height	192 mm
Width	164 mm
Depth	105 mm
Internal height	175 mm
Internal width	150 mm
Internal depth	100 mm
Enclosure mounting	Wall mounted
Device composition	1 body 1 cover 4 cover screw
Body type	One piece moulded
Type of front cover	Low transparent cover
Cover fixing	Plastic screws
Lock type	Captive screw flat outside sealed area
Removable parts	Cover by captive screws

Complementary

Material	Polycarbonate
Colour	Grey (RAL 7035) Transparent
Standards	UL 508 A IEC 62208
Product certifications	TÜV[RETURN]UL
Electrical insulation class	Class II
Mounting location	Outdoor (with canopy or shelter and anticondensation valve)
Net weight	0.6 kg







Environment

IP degree of protection	IP66 conforming to NEMA 4.4X
IK degree of protection	IK08 conforming to IEC 62262
Fire resistance	960 °C
Ambient air temperature for storage	-15...60 °C
Operating temperature	-25...80 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10.5 cm
Package 1 Width	16.4 cm
Package 1 Length	19.3 cm
Package 1 Weight	600 g
Unit Type of Package 2	CAR
Number of Units in Package 2	17
Package 2 Height	40 cm
Package 2 Width	40.5 cm
Package 2 Length	60 cm
Package 2 Weight	11.2 kg
Unit Type of Package 3	PAM
Number of Units in Package 3	425
Package 3 Height	214 cm
Package 3 Width	100 cm
Package 3 Length	120 cm
Package 3 Weight	295 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information

Contractual warranty

Warranty	18 months
----------	-----------