

Product data sheet

Characteristics

NSYTBP19168

Thalassa, PC box IP66 IK08 RAL7035
 Int.H175W150D80 Ext.H193W164D87 Opaque
 PC cover H20



Main

Range	Thalassa
Product name	Thalassa TBP
Device application	Multi-purpose
Category	Industrial box
Height	192 mm
Width	164 mm
Depth	87 mm
Internal height	175 mm
Internal width	150 mm
Internal depth	80 mm
Enclosure mounting	Wall mounted
Device composition	1 body 1 cover 4 cover screw
Body type	One piece moulded
Type of front cover	Low plain cover
Cover fixing	Plastic screws
Lock type	Captive screw flat outside sealed area
Removable parts	Cover by captive screws

Complementary

Material	Polycarbonate
Colour	Grey (RAL 7035)
Standards	IEC 62208 UL 508 A
Product certifications	TÜV[RETURN]JUL
Electrical insulation class	Class II
Mounting location	Outdoor (with canopy or shelter and anticondensation valve)
Net weight	0.45 kg

Environment

IP degree of protection	IP66 conforming to NEMA 4.4X
IK degree of protection	IK08 conforming to IEC 62262
Fire resistance	960 °C
Ambient air temperature for storage	-15...60 °C
Operating temperature	-25...80 °C

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10.0 cm
Package 1 Width	17.0 cm
Package 1 Length	20.5 cm
Package 1 Weight	503.0 g
Unit Type of Package 2	CAR
Number of Units in Package 2	20
Package 2 Height	40.5 cm
Package 2 Width	40.5 cm
Package 2 Length	60.5 cm
Package 2 Weight	10.8 kg
Unit Type of Package 3	P12
Number of Units in Package 3	240
Package 3 Height	120 cm
Package 3 Width	80 cm
Package 3 Length	135 cm
Package 3 Weight	141 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Contractual warranty

Warranty	18 months
----------	-----------