

Product data sheet

Characteristics

SRVS1KI-AZ

Easy UPS 1 Ph On-Line, Tower, 1000VA, 230V, 2x Australian outlets, Intelligent Card Slot, LCD



Overview

Presentation	For small to medium businesses, Easy UPS 1 Ph On-Line provides essential power protection for unstable power conditions, ensuring consistent and reliable connectivity at the most critical moments.
Lead time	Usually in Stock

Main

Main Input Voltage	230 V
Product or component type	Uninterruptible power supply (UPS)
Other Input Voltage	220 V 240 V
Main Output Voltage	230 V
Other Output Voltage	220 V 240 V
Rated power in W	800 W
Rated power in VA	1000 VA
Input Connection Type	IEC 60320 C14
Output connection type	2 Australian
Cable length	1.48 m
Number of cables	1
Provided equipment	1 IEC 60320 C13 to Australian power cable 1 USB cable 1 RS-232 configuration cable User manual

Batteries & Runtime

Battery type	Lead-acid battery
Battery voltage	24 V
Number of battery filled slots	0
Number of battery free slots	0
Battery recharge time	4 h
Battery life	3...5 year(s)
Battery charger power	38 W rated

General

Number of power module filled slots	0
Number of power module free slots	0
Redundant	No

Physical

Colour	Black (RAL 7010)
Height	22.3 cm
Width	14.5 cm
Depth	28.8 cm
Net weight	9.3 kg
Mounting location	Front
Mounting preference	No preference
Mounting mode	Not rack-mountable
USB compatible	Yes
Mounting position	Vertical

Input

Input voltage limits	110...285 V half load 160...280 V full load
Network frequency	40...70 Hz auto sensing

Output

Maximum configurable power in VA	1000 VA
Maximum configurable power in W	800 W
Output frequency	50/60 Hz +/- 3 Hz sync to mains
UPS type	Double conversion online
Wave type	Sine wave
Additional information	Configurable for 220 : 230 or 240 nominal output voltage
Bypass type	Internal bypass (automatic and manual)
Crest factor	3 : 1

Conformance

Product certifications	CE
Standards	EN/IEC 62040-1:2019/A11:2021 EN/IEC 62040-2:2006/AC:2006 EN/IEC 62040-2:2018

Environmental

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 % non-condensing
Operating altitude	0...3000 m
Ambient air temperature for storage	-20...50 °C
Storage Relative Humidity	0...95 % non-condensing
Storage altitude	0...15000 m
Acoustic level	50 dBA
IP degree of protection	IP20

Communications & Management

Alarm	Alarm when on battery : distinctive low battery alarm : configurable delays
Free slots	1
Control panel	Multifunction LCD status and control console

Surge Protection and Filtering

Surge energy rate	600 J
-------------------	-------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	33 cm
Package 1 Width	23.5 cm
Package 1 Length	36.5 cm
Package 1 Weight	10.6 kg

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------