

Product data sheet

Characteristics

NSYTRAL22

Linery, Plug-in bridge, Linery TR, 2 points, for 2.5mm² terminal blocks, 2 way, red, set of 50



Main

Range	Linery
Product name	Linery TR
Product or component type	Plug-in bridge
Device short name	TRA
Accessory / separate part category	Connection accessory
Product compatibility	TRV screw terminal terminal block TRP push-in terminal block TRH IDC terminal block TRR spring terminal - passthrough terminal block TRR spring terminal - protective earth terminal block, length = 78 mm TRR spring terminal - blade disconnect terminal block TRR spring terminal - removable carrier disconnect terminal block
Number of ways	2 ways

Complementary

Cable cross section	2.5 mm ²
Number of connections	3 4 2
Number of measurement input	2 6 1 3 4
Quantity per set	Set of 50
Net weight	1.7 g
Colour	Red

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.000 cm
Package 1 Width	4.000 cm
Package 1 Length	13.000 cm
Package 1 Weight	0.900 g
Unit Type of Package 2	BB1
Number of Units in Package 2	50
Package 2 Height	2.000 cm
Package 2 Width	4.000 cm
Package 2 Length	13.000 cm
Package 2 Weight	84.000 g
Unit Type of Package 3	S01

Number of Units in Package 3	1750
Package 3 Height	15.000 cm
Package 3 Width	15.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	3.136 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Circularity Profile	No need of specific recycling operations
Halogen content performance	Halogen free plastic parts product

Contractual warranty

Warranty	18 months
----------	-----------