

## Product data sheet

### Characteristics

# NSYTRAL23

Lineryy, Plug-in bridge, Lineryy TR, 3 points, for 2.5mm<sup>2</sup> terminal blocks, red, 3 way, set of 50



### Main

Range	Lineryy
Product name	Lineryy TR
Product or component type	Plug-in bridge
Device short name	TRA
Accessory / separate part category	Connection accessory
Product compatibility	TRV screw terminal terminal block TRP push-in terminal block TRR spring terminal terminal block TRH IDC terminal block
Number of ways	3 ways

### Complementary


Cable cross section	2.5 mm <sup>2</sup>
Number of connections	3 4 2
Number of measurement input	3 1 4 6 2
Quantity per set	Set of 50
Net weight	2.5 g
Colour	Red

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.300 cm
Package 1 Width	1.500 cm
Package 1 Length	2.300 cm
Package 1 Weight	2.000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	50
Package 2 Height	1.500 cm
Package 2 Width	8.000 cm
Package 2 Length	12.000 cm
Package 2 Weight	128.000 g
Unit Type of Package 3	S01
Number of Units in Package 3	1500
Package 3 Height	15.000 cm
Package 3 Width	15.000 cm

Package 3 Length	40.000 cm
Package 3 Weight	3.986 kg

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 <a href="#">Yes</a>
Circularity Profile	No need of specific recycling operations
Halogen content performance	Halogen free plastic parts product

### Contractual warranty

Warranty	18 months
----------	-----------