


## Product data sheet

### Characteristics

# NSYTRV44D

Linergy, Screw Terminal, Double Level, 4 Points, 4mm<sup>2</sup>, Grey



### Main

Range	Linergy
Product name	Linergy TR
Product or component type	Terminal block
Device short name	TRV
Accessory / separate part categor	Connection accessory
Terminal block type	Passthrough
Terminal block level	2
Mounting mode	Clip-on
Nominal cross section	4 mm <sup>2</sup>
Length	69.9 mm
Colour	Grey
Quantity per set	Set of 50

### Complementary

Width	6.2 mm
Height	65 mm
Connections - terminals	1 x screw terminal: upstream (M3) 1 x screw terminal: downstream (M3)
Number of connections	2
Connection position	Sideways
Number of measurement input	4
Cable cross section	0.14...6 Mm <sup>2</sup> , solid cable with cable end 0.2...4 Mm <sup>2</sup> , flexible cable with cable end 0.14...6 Mm <sup>2</sup> , flexible cable without cable end 0.14...6 mm <sup>2</sup> , solid cable without cable end
Tightening torque	0.6...0.8 N.m
Wire stripping length	9 mm
Tool type	Connection: screwdriver Disconnection: screwdriver
[Ue] rated operational voltage	600 V CSA[RETURN]600 V cURus[RETURN]800 V conforming to EN/IEC 60947-7-1[RETURN]440 V conforming to ATEX Exe II Ex II 2 GD
[In] rated current	30 A CSA 30 A cURus 30 A conforming to EN/IEC 60947-7-1 25.5 A conforming to ATEX Exe II Ex II 2 GD
Material	Polyamide 6/6: insulating case Copper alloy: connector and screw Copper alloy: commoning link Chromium-nickel steel: spring
Dielectric loss	0.01 at 1 MHz conforming to IEC 60250 0.01 at 1 MHz conforming to VDE 0303-T4
Dielectric constant	3.7 at 1 MHz
Resistivity	10000 MΩ.M conforming to IEC 60093 10000 MΩ.m conforming to VDE 0303-T30
Surface resistance	1000 GΩ conforming to IEC 60093 1000 GΩ conforming to VDE 0303-T30

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Creep resistance	500 CTI (> 400 kV) conforming to IEC 60093 500 CTI (> 400 kV) conforming to VDE 0303-T30
Flame retardance	V0, thickness 0.8 mm conforming to UL 94
Net weight	17 g
Range compatibility	Prisma G Prisma P Prisma PH Prisma Pack Spacial Kaedra Pragma TeSys
Product compatibility	Spacial enclosures

## Environment

Product certifications	LR[RETURN]IEC- Ex[RETURN]EAC[RETURN]GL[RETURN]ATEX[RETURN]cURus[RETURN]DNV[RETURN]CSA
Dielectric strength	1000 V conforming to IEC 60243-1
Ambient air temperature for operation	-40...130 °C conforming to IEC 60216-1 -40...130 °C conforming to VDE 0304-T21

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7 cm
Package 1 Width	7.8 cm
Package 1 Length	32 cm
Package 1 Weight	19 g
Unit Type of Package 2	BB1
Number of Units in Package 2	50
Package 2 Height	7 cm
Package 2 Width	7.8 cm
Package 2 Length	32 cm
Package 2 Weight	978 g
Unit Type of Package 3	S03
Number of Units in Package 3	450
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	9.276 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 <a href="#">Yes</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Halogen content performance	Halogen free plastic parts product

## Contractual warranty

Warranty	18 months
----------	-----------