

Product data sheet

Characteristics

VW3A3609

Devicenet communication module, Altivar 32

Main

Range of product	Altivar
Product or component type	Communication module

Complementary

Range compatibility	Altivar Process Modular Altivar 32 Altivar&Nbsp;Process ATV600 Altivar Machine ATV340 except Sercos drives Altivar&Nbsp;Process ATV900 Altivar Machine ATV320
Communication port protocol	DeviceNet
Electrical connection	1 connector 1 removable 5-way screw connector
Transmission rate	125 kbps, 250 kbps and 500 kbps configurable
Maximum cable distance between devices	100 M for 500 kbps 500 m for 125 kbps
Addressing	1...63 configurable by graphic terminal/SoMove software
Communication service	Inputs : polled, change of state, cyclic Outputs : polled ODVA AC drive and CiA 402 profile Auto device replacement Communication monitoring time out adjustable by DeviceNet configurator
Display type	1 LED for MS (Module Status) 1 LED for NS (Network Status)
Diagnostic function	Control mode received by graphic terminal Received instruction by graphic terminal
Bus profile	CIP AC Drive CiA 402
Net weight	0.3 kg

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.700 cm
Package 1 Width	6.200 cm
Package 1 Length	8.900 cm
Package 1 Weight	67.000 g
Unit Type of Package 2	S03
Number of Units in Package 2	100
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm

Package 2 Length	40.000 cm
Package 2 Weight	7.098 kg

Offer Sustainability

Packaging without single use plastic	No
Packaging made with recycled cardboard	Yes
SCIP Number	2a2f2e41-9976-44a1-aaef-cecaebe1de88
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
Take-back	No

Contractual warranty

Warranty	18 months
----------	-----------