

## Product data sheet

### Characteristics

# WHB120-RG

## SWITCH 1 GANG 1 POLE H/PROOF 250V 20A. WHB120, RG REPLACES CSS120, GY



### Main

Range of product	Weathershield
Product brand	Clipsal
Device presentation	Basic element with complete housing

### Complementary

Switch function	1-pole
Number of poles	1
Device mounting	Surface
Fixing mode	By screws
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	20 A
Marking	ON-OFF
Marking location	Marking on surface




### Environment

Standards	AS 60529 AS/NZS 60947-3 IEC 60669-1 AS/NZS 3947-3:approval number S/1
-----------	--

### Packing Units

Package 1 Weight	497.000 g
Package 1 Height	85.000 mm
Package 1 width	97.000 mm
Package 1 Length	170.000 mm

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes

---

China RoHS Regulation

 [China RoHS Declaration](#)

---

Environmental Disclosure

 [Product Environmental Profile](#)

---