

Product data sheet

Characteristics

WMS320R

Metal Clad, Reversing Switch, 3 Pole, 20A, 415V, Made of Cast Aluminium



Main

Range of product	Wilco Series A
Product brand	Clipsal
Device presentation	Basic element with complete housing

Complementary

Switch function	3-pole
Control type	Rotary knob
Number of poles	3
Device mounting	Base mounting
Fixing mode	By screws
Material	Cast aluminium
Local signalling	without
[Ue] rated operational voltage	415 V AC
Rated current	20 A
Marking	ON-OFF
Marking location	Marking on surface

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	12.8 cm
Package 1 Width	10.0 cm
Package 1 Length	14.9 cm
Package 1 Weight	1.1117 kg
Unit Type of Package 2	CAR
Number of Units in Package 2	5
Package 2 Height	23.7 cm
Package 2 Width	20.3 cm
Package 2 Length	30 cm
Package 2 Weight	5.85 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile