

Product data sheet

Characteristics

RCD440/30

Residual current circuit breaker, Clipsal - Max 4, 4P 40 A 30mA Type AC 415 V

Main

Range	Resi MAX
Product or component type	Residual current circuit breaker (RCCB)
Product brand	Clipsal
Device application	Protection
Poles description	4P
Number of modules	4
[In] rated current	40 A
Network type	AC
Earth-leakage sensitivity	30 mA
Earth-leakage protection class	Type AC

Complementary

[Ue] rated operational voltage	415 V AC
[Uimp] rated impulse withstand voltage	6 kV
Size	81 x 72 x 75 mm conforming to DIN 43880

Environment

Standards	AS/NZS 61008
IP degree of protection	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529
Ambient air temperature for operation	-5...40 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.0 cm
Package 1 Width	8.0 cm
Package 1 Length	9.0 cm
Package 1 Weight	366.0 g

Offer Sustainability

SCIP Number	2c7837a4-39fc-4abc-96ed-2ef14f8f87c7
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	67