

## Product data sheet

### Characteristics

# XVBC07

Harmony XVB, Base unit for modular tower lights, plastic, black, 70mm, bottom or side cable entry



### Main

|                           |                                       |
|---------------------------|---------------------------------------|
| Range of product          | Harmony XVB Universal                 |
| Product or component type | Base unit                             |
| Component name            | XVBC                                  |
| Material                  | Glass reinforced polyamide: base unit |

### Complementary

|                               |  |
|-------------------------------|--|
| Fixing mode                   | Direct or tube fixing  |
| Mounting diameter             | 70 mm  |
| Product destination           | Banks without flash discharge tube unit                                      |
| Electrical connection         | 1 connector for standard input   |
| Cable entry                   | Bottom or side entry   |
| Assembly style                | Customer assembly, up to 5 units   |
| Terminals description ISO n°1 | (COM-2)PW<br>(COM-3)PW<br>(COM-1)PW<br>(GND)GROUND<br>(COM-4)PW<br>(COM-5)PW |
| Net weight                    | 0.16 kg  |

### Environment

|                                     |   |
|-------------------------------------|---|
| Product certifications              | CCC<br>EAC<br>CSA C22-2 No 14<br>UL 508 |
| Standards                           | EN/IEC 60947-5-1                        |
| Protective treatment                | TC                                      |
| Ambient air temperature for storage | -40...70 °C                             |
| NEMA degree of protection           | Type 4X conforming to UL (indoor)       |

### Packing Units

|                              |       |
|------------------------------|-------|
| Unit Type of Package 1       | PCE   |
| Number of Units in Package 1 | 1     |
| Package 1 Height             | 10 cm |
| Package 1 Width              | 12 cm |
| Package 1 Length             | 10 cm |
| Package 1 Weight             | 170 g |
| Unit Type of Package 2       | S03   |

|                              |         |
|------------------------------|---------|
| Number of Units in Package 2 | 36      |
| Package 2 Height             | 30 cm   |
| Package 2 Width              | 30 cm   |
| Package 2 Length             | 40 cm   |
| Package 2 Weight             | 7 kg    |
| Unit Type of Package 3       | P06     |
| Number of Units in Package 3 | 144     |
| Package 3 Height             | 45 cm   |
| Package 3 Width              | 60 cm   |
| Package 3 Length             | 80 cm   |
| Package 3 Weight             | 36.5 kg |

## Offer Sustainability

|                            |   |
|----------------------------|---|
| Sustainable offer status   | Green Premium product   |
| REACH Regulation           | <a href="#">REACH Declaration</a>   |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>                              |
| Mercury free               | Yes   |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>  |
| RoHS exemption information | <a href="#">Yes</a>   |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>   |
| WEEE                       | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |


## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Indicator Bank with "Flash" Discharge Tube Unit

Dimensions

Below drawing shows the minimum configuration of the product. Select the number of stages according to the product characteristics in order to get b dimension.



- (1) Base unit
- (2) Illuminated or audible signalling unit XVBC•••, to be ordered separately
- (3) "Flash" unit XVBC•••, to be ordered separately


| Number of illuminated or audible signalling units other than "flash" tube | b in mm | b in in. |
|---|---------|----------|
| 1   | 295     | 11.61    |
| 2   | 358     | 14.09    |
| 3   | 421     | 16.57    |
| 4   | 484     | 19.06    |

---

## Base Unit for Indicator Banks

---

### Panel Cut-out for Direct Fixing



---

## Illuminated Beacon

---

### Wiring Diagram

