

Product data sheet

Characteristics

RMXE108S

Consumer switchboard, Clipsal Resi MAX, 1 row 8 modules Surface Mounted

Main

Range	Resi MAX
Product brand	Clipsal
Product or component type	Enclosure
Enclosure type	Mini enclosure for modular device
Device application	Distribution
Number of 18 mm modules per row	8
Provided equipment	DIN rail Earth terminal block Neutral terminal block
Type of front cover	Plain
Colour	White (RAL 9003)
Door type	Plain door

Complementary

Enclosure mounting	Surface
Number of horizontal rows	1
[In] rated current	63 A
Number of ways	8 ways
Cable entry	Knock-out top and bottom Knock-out rear
Type of rail	35 mm asymmetrical rail
Number of terminal blocks	8 earth (screw connection) 10 neutral (screw connection)
Enclosure material	Technoplastic
Width	196 mm external
Height	228 mm external
Depth	101.5 mm external

Environment

Fire resistance	650 °C
IP degree of protection	IP40
IK degree of protection	IK07

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11.2 cm
Package 1 Width	21.0 cm
Package 1 Length	25.0 cm
Package 1 Weight	0.75 kg
Unit Type of Package 2	P12
Number of Units in Package 2	135
Package 2 Height	80.0 cm
Package 2 Width	80.0 cm

Package 2 Length	120.0 cm
Package 2 Weight	113.25 kg

Offer Sustainability

Packaging without single use plastic	No
Packaging made with recycled cardboard	No
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
Take-back	No