

Product data sheet

Characteristics

SAU2506443NDF

SAU Chassis, Acti9, 250A, 3Ph+N, 64 poles, 18mm for iC60 MCB and RCBO, dual feed

Main

| | |
|---------------------------|--------------|
| Range | Acti9 |
| Product or component type | Chassis |
| Device application | Distribution |

Complementary

| | |
|--|---------------------------|
| Range compatibility | Acti 9 distribution board |
| Network type | AC |
| [In] rated current | 250 A |
| Number of ways | 1 way (incomer) - 3P + N |
| Rated voltage | 415 V 50 Hz |
| Short-circuit withstand | 25 kA 0.1 s |
| [Ui] rated insulation voltage | 500 V |
| [Uimp] rated impulse withstand voltage | 6 kV |
| Number of poles | 64 |
| Number of poles | 64 x 18 mm |
| Width | 215 mm |
| Length | 578 mm |
| Busbar pitch | 18 mm |
| Location of connection | Dual feed |

Environment

| | |
|-----------|--------------|
| Standards | AS/NZS 61439 |
|-----------|--------------|

Packing Units

| | |
|------------------------------|---------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 9.5 cm |
| Package 1 Width | 24.5 cm |
| Package 1 Length | 86.2 cm |
| Package 1 Weight | 5.9 kg |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

| | |
|----------------------------|--|
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| Mercury free | Yes |
| China RoHS Regulation | China RoHS Declaration |
| RoHS exemption information | Yes |