



## Main

Range	Clipsal Iconic
Product or component type	Switched socket
Device presentation	Complete product
Outlet poles configuration	2P + E with shutter
Outlet standard	Australian

## Complementary

Device mounting	Flush
Number of power socket outlets	4
Number of rocker	4
Range compatibility	Clipsal Iconic
Outlet standard description	With earthing contact
Outlet standard	Australian/New Zealand
Ground lug position	Straight 180° position
Number of gangs	2 gangs
Fixing mode	By screw
Installation direction	Horizontal
Surface finish	Matt
Type of packing	Polybag
Quantity per set	Set of 1
Sale per indivisible quantity	1
Rated current	10 A at 250 V AC 50 Hz
Electrical durability	12000 cycles
Connections - terminals	3 screw terminals
Screwdriver shape	Square drive no 1 (SQ1) Philips No 2
Clamping connection capacity	1 x 2.5...4 x 2.5 mm <sup>2</sup> for rigid cable(s) 1 x 2.5...4 x 2.5 mm <sup>2</sup> for stranded cable(s) 1 x 2.5...4 x 2.5 mm <sup>2</sup> for flexible cable(s)
Wire stripping length	16 mm
Material	PC (polycarbonate): fixing frame PP (polypropylene): rocker POM (polyoxymethylene): shutter PC (polycarbonate): cover frame ABS (acrylonitrile butadiene-styrene): cover frame POM (polyoxymethylene): locking bar
Height	78 mm
Width	216 mm
Depth	30 mm
Embedding depth	18 mm
Net weight	0.216 kg

## Environment

Ambient air temperature for operation	0...45 °C
Relative humidity	10...95 %
Standards	AS/NZS 3112
Product certifications	RCM

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3 cm
Package 1 Width	21 cm
Package 1 Length	7.8 cm
Package 1 Weight	212.8 g

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
Sustainable packaging	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations