


## Product data sheet

### Characteristics

# SAU250H483DF

Acti9, SAU hybrid Chassis, Acti9, 250A, 3Ph, 36 poles 18mm and 12 poles 27mm for MCB and RCBO, dual feed



### Main

Range	Acti9
Product or component type	Chassis
Device application	Distribution

### Complementary

Range compatibility	Acti 9 distribution board
Network type	AC
[In] rated current	250 A
Number of ways	1 way (incomer) - 3P
Rated voltage	415 V 50 Hz
Short-circuit withstand	25 kA 0.1 s
[Ui] rated insulation voltage	500 V
[Uimp] rated impulse withstand voltage	6 kV
Number of poles	48
Number of poles	12 x 27 mm 36 x 18 mm
Width	215 mm
Length	488 mm
Busbar pitch	27 Mm 18 mm
Location of connection	Dual feed

### Environment

Standards	AS/NZS 61439
-----------	--------------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.5 cm
Package 1 Width	24.5 cm
Package 1 Length	77.2 cm
Package 1 Weight	4.3 kg

## Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 <a href="#">Yes</a>