

## Product data sheet

### Characteristics

# SAU250H963

Acti9, SAU hybrid Chassis, Acti9, 250A, 3Ph, 84 poles 18mm and 12 poles 27mm for MCB and RCBO, top or bottom

#### Main

Range	Acti9
Product or component type	Chassis
Device application	Distribution

#### Complementary

Range compatibility	Acti 9 distribution board
Network type	AC
[In] rated current	250 A
Number of ways	1 way (incomer) - 3P
Rated voltage	415 V 50 Hz
Short-circuit withstand	25 kA 0.1 s
[Ui] rated insulation voltage	500 V
[Uimp] rated impulse withstand voltage	6 kV
Number of poles	96
Number of poles	12 x 27 mm 84 x 18 mm
Width	215 mm
Length	920 mm
Busbar pitch	27 Mm 18 mm
Location of connection	Top or bottom

#### Environment

Standards	AS/NZS 61439
-----------	--------------

#### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.5 cm
Package 1 Width	24.5 cm
Package 1 Length	111.2 cm
Package 1 Weight	7.1 kg

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>